



2 Way 40A 30mA RCCB Incomer Fitted with + 1x 32A & 1x 6A MCB

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	No
Overvoltage protection	Yes

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	2
-------------------	---

Electric current

Rated current IN	40 A
------------------	------

Weight

Weight	2 kg
--------	------

Dimensions

Depth	102.50 mm
Internal depth	80 mm
Height	240 mm
Width	149 mm
Thickness of sidewall	1 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of conduit inlets	0
Number of accessible phases	1

Scope of delivery

Number of RCCB in enclosure	1
-----------------------------	---

Equipment

Number of groups	0
Number of light groups	0
Number of rows	1
With energy meter	No
Number of rails	1
Extension possible	No
With bell transformer	No
With socket outlet	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP4X

Safety

Number of earth leakage switches 30 mA	1
Number of earth leakage switches 300 mA	0

Compatibility

Cooker group suitable as power current group	No
--	----

Sustainability

RoHS conform	Yes
--------------	-----