



JKD2884TM

200A Power/Lighting/Mechanical Board 8/8/4 Way Pan Assemblies Modbus

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	3
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	No

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Capacity

Number of modules	60
-------------------	----

Electric current

Rated current	200 A
---------------	-------

Dimensions

Depth	165.50 mm
Height	1550 mm
Width	465 mm
Thickness of sidewall	0.90 mm

Cover, door

Interlockable	No
Door/cover is transparent	Yes

Materials

RAL code	7035
Material	Steel

Connection

Number of accessible phases	3
-----------------------------	---

Equipment

With energy meter	Yes
Extension possible	Yes

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30