



35623502

Control on/off switch 2p impr. Heizung-0-I surf.-mtd, lens, W.1, p.wh.m.plas. LT

Technical Features

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|---------------|
| Colour | Polar white |
| RAL code | 9010 |
| Surface finish | Matt |
| Material | Thermoplastic |
| Treatment | Untreated |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Dimensions

| | |
|------------------------------------|------------|
| Dimensions | 55 x 55 mm |
| Built-in depth flush-mounted boxes | 0 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP55 |
| Impact resistance IK | IK07 |

Texts

| | |
|--------------------|---|
| Installation mode | For screw fastening |
| Type of connection | With plug-in terminals |
| Lighting | With red 230 V LED unit For monitoring circuit |
| Switch mode | 2-pole |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |