



35623502

Control on/off switch 2p impr. Heizung-0-I surf.-mtd, lens, W.1, p.wh.m.plas. LT

Technical Features

Electric current

Switching current	10 A
-------------------	------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Connectivity

Mounting type	Screw mounting
---------------	----------------

Dimensions

Dimensions	55 x 55 mm
Built-in depth flush-mounted boxes	0 mm

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK07

Texts

Installation mode	For screw fastening
Type of connection	With plug-in terminals
Lighting	With red 230 V LED unit For monitoring circuit
Switch mode	2-pole

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes