



50453512

Push-button insert, NOcontact rocker surf.-mtd/flush-mtd, W.1, p.white m plas LT

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Rocker
---------------------------	--------

Materials

Colour	Polar white
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	70 mm
Width	70 mm
Depth	45 mm
Built-in depth flush-mounted boxes	0 mm

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Type of connection	With plug-in terminals

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes