



41236086

**SCHUKO socket outlet, Q.1/Q.3/Q.7, anthracite velvety, lacquered**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

RAL code 7021

Surface finish Velvety

Treatment Varnished

**Dimensions**

Width 71 mm

Built-in depth flush-mounted boxes 40 mm

Built-in depth 32 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

**Accessories**

Has labelling field No

**Cover, door**

Type of lid Without lid

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection Yes

Impact resistance IK IK02

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

**Texts**

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With screw-in lift terminals

**Suitable for**

---

Q.x

---