



41236086

SCHUKO socket outlet, Q.1/Q.3/Q.7, anthracite velvety, lacquered

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Voltage

| | |
|-----------------|-------------|
| Rated voltage | 250 V |
| Nominal voltage | 250 - 250 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Materials

| | |
|----------------|-----------|
| RAL code | 7021 |
| Surface finish | Velvety |
| Treatment | Varnished |

Dimensions

| | |
|------------------------------------|-------|
| Width | 71 mm |
| Built-in depth flush-mounted boxes | 40 mm |
| Built-in depth | 32 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type | Screw mounting |

Equipment

| | |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert | No |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Cover, door

| | |
|-------------|-------------|
| Type of lid | Without lid |
|-------------|-------------|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Safety

| | |
|----------------------------------|------|
| With enhanced contact protection | Yes |
| Impact resistance IK | IK02 |
| Ingress Protection (IP) class | IP20 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Texts

| | |
|--------------------|------------------------------|
| Imprint | Without imprint |
| Cover | Central cover plate |
| Protection | Enhanced contact protection |
| Type of connection | With screw-in lift terminals |

Suitable for

| | |
|-----|--|
| Q.x | |
|-----|--|