



50413512



Push-button insert, NOcontact rocker surf.-mtd/flush-mtd, W.1, p.white m plas LT

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Rocker

Materials

Colour Polar white

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

Dimensions

Height 80 mm

Width 80 mm

Depth 32 mm

Built-in depth flush-mounted boxes 0 mm

Height of P-touch band for labelling field 12 mm

Installation, mounting

Mounting on Flush mounting
Surface mounting

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK05

Accessories

Has labelling field Yes

Use conditions

Operating temperature -25 - 35 °C

Texts

Imprint Without imprint

Installation mode For screw fastening

Lighting With blue 230 V LED unit

Terminal Wago clip-in 3-wire connection terminal for wiring

Type of connection With N-terminal
With plug-in terminals

Sustainability

REACH-SVHC free Yes

RoHS conform Yes