



30483512

Double change-over switch insert rocker 2g surf/flushmtd,isolated input W1 wh LT

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting
Surface mounting

Voltage

Rated voltage 250 V

Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Identification

Assembly arrangement Control element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 70 x 70 mm

Built-in depth 12 mm

Built-in depth flush-mounted boxes 0 mm

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK05

Architecture

Control/operation element Double rocker

Electric current

Rated current 10 A

Connection

Connector/plug type Bayonet latch

Texts

Installation mode For screw fastening

Type of connection With plug-in terminals

Lighting Without lighting (cannot be illuminated)

Switch mode Change-over contact/Change-over switch

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes