



31763502

**Control change-over switch surface-mtd, lens, W.1, p. white, matt, plastic LT**

**Technical Features**

**Electric current**

Switching current	10 A
-------------------	------

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Identification**

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	76 x 76 mm
Built-in depth	0 mm
Built-in depth flush-mounted boxes	0 mm

**Electric current**

Rated current	10 A
---------------	------

**Texts**

Installation mode	For screw fastening
Type of connection	With N-terminal With plug-in terminals
Lighting	With red 230 V LED unit For monitoring circuit

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes