



50423515



Push-button insert, 2 NO contacts rocker 2g surf./flushmtd comm. input ,W1, grey

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Double rocker

Materials

Colour Grey

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

Dimensions

Height 71 mm

Width 71 mm

Depth 53 mm

Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Flush mounting
Surface mounting

Controls and indicators

Number of buttons 1

Type of push button Series push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK05

Accessories

Has labelling field No

Use conditions

Operating temperature -25 - 35 °C

Texts

Imprint Without imprint

Installation mode For screw fastening

Type of connection With plug-in terminals

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes