



50423515



Push-button insert,2 NO contacts rocker 2g surf./flushmtd comm. input ,W1,grey

#### Technical Features

##### Electric current

Momentary contact current	10 A
---------------------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Architecture

Control/operation element	Double rocker
---------------------------	---------------

##### Materials

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

##### Dimensions

Height	71 mm
Width	71 mm
Depth	53 mm
Built-in depth flush-mounted boxes	0 mm

##### Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

##### Controls and indicators

Number of buttons	1
Type of push button	Series push button
With feedback signal contact	No

##### Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

##### Accessories

Has labelling field	No
---------------------	----

##### Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

##### Texts

Imprint	Without imprint
Installation mode	For screw fastening
Type of connection	With plug-in terminals

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes