



6768803522

sock.outl. insert w. earth.pin a. hing. cov. SM/flush-mounted, cont.prot., W1

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Metal Plastic Thermoplastic
Treatment	Untreated

##### Dimensions

Height	71 mm
Width	71 mm
Depth	48 mm
Built-in depth flush-mounted boxes	35 mm

##### Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No

##### Accessories

Has labelling field	Yes
---------------------	-----

##### Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	------------------------------------------------------------

##### Capacity

Number of modules	1
-------------------	---

##### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55

##### Functions

With orientation lighting	No
With function lighting	No

<b>Texts</b>	
Imprint	Without imprint
Cover	Complete housing
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes