



50453515

**Push-button insert, NO contact rocker surface-mtd/flush-mtd, W.1, grey matt LT**

**Technical Features**

**Electric current**

Momentary contact current	10 A
---------------------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Rocker
---------------------------	--------

**Materials**

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

**Dimensions**

Height	70.90 mm
Width	70.90 mm
Depth	41.50 mm
Built-in depth flush-mounted boxes	0 mm

**Installation, mounting**

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

**Controls and indicators**

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-25 - 35 °C
-----------------------	-------------

**Texts**

Imprint	Without imprint
Installation mode	For screw fastening
Type of connection	With plug-in terminals

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes