



60060

**Universal load shedder 3 rotary channels, 3 modules**

**Technical Features**

**Frequency**

Frequency 50 - 50 Hz

**Capacity**

Number of modules 3

**Use conditions**

Operating temperature 0 - +50 °C

Storage/transport temperature -20 - +60 °C

**Dimensions**

Height 80 mm

Width 52 mm

Depth 60 mm

**Sustainability**

RoHS conform Yes

**Illustrations | Drawings**

