



30763525

Illuminated change-over switch surface-mtd, lens, W.1, grey/light grey matt LT

Technical Features

Electric current

Switching current	10 A
-------------------	------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Identification

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	76 x 76 mm
Built-in depth	0 mm
Built-in depth flush-mounted boxes	0 mm

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	10 A
---------------	------

Texts

Installation mode	For screw fastening
Type of connection	With N-terminal With plug-in terminals
Lighting	With blue 230 V LED unit For illumination
Switch mode	Change-over

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes