



50763555



Push-button, change-over contact surface-mtd, W.1, grey/light grey matt LT

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Single rocker
Number of poles	1

Materials

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	55.50 mm
Width	55.50 mm
Depth	27.80 mm
Built-in depth flush-mounted boxes	0 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Lighting	With blue 230 V LED unit
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
Type of connection	With N-terminal With plug-in terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes