



VB118R

Small distributor,vega,surface,1row,18M,IP40,QC-terminal,PE,transparent door

Technical Features

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 90 A

Equipment

Number of rails 1

Number of rows 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 18

Dimensions

Height 325 mm

Width 400 mm

Depth 146 mm

Cover, door

Number of cabinet doors 1

Number of locks 1

Dimensions

Number of width units 18

Cover, door

Door/cover is transparent Yes

Materials

Material Polystyrene (PS)

RAL code 9010

Colour White

Equipment

Has earthing terminal block Yes

Has mounting plate No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP40

Locking type Snap on lock
Without lock

Glow wire test 650 °C

Sustainability

RoHS conform Yes