



VB318R

Small distributor,vega,surface,3row,54M,IP40,QC-terminal,PE,transparent door

### Technical Features

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	3
Number of rows	3
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	54
-------------------	----

#### Dimensions

Height	625 mm
Width	400 mm
Depth	146 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	1

#### Dimensions

Number of width units	18
-----------------------	----

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Connectivity

Mounting type	Surface mounting
---------------	------------------

#### Materials

Material	Polystyrene (PS)
RAL code	9010
Colour	White

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

#### Sustainability

RoHS conform	Yes
--------------	-----