



WBMDUR

Mechanism rotary dimmer trailing-edge

Technical Features

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Material Polycarbonate (PC)

Dimensions

Height 24 mm

Width 24 mm

Depth 65 mm

Architecture

Control/operation element Push & rotary switch

Power

Power consumption standby 0.10 W

Lighting

Dimmable 230 V LED lamp 3 - 250 W

LED lamp power 250 W

Use conditions

Operating temperature -5 - 45 °C

Capacity

Number of modules 1

Texts

Dimming principle Phase cut-off

Fuse Short-circuit and overload-proof (electronic fuse)

Installation mode RotoLoc®

Type of connection With screw terminals

Extension unit input With extension unit input for slave push-button WBMESL

Operation and control No Bluetooth interface

Equipment

Substation input Yes

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes