



K7B1M075W

**6A Luminaire Lead 1.5m 0.75mm 3 Core Plug to Wire**

**Technical Features**

**Architecture**

Number of poles	2
-----------------	---

**Voltage**

Max. operating voltage	240 V
------------------------	-------

**Electric current**

Rated current	6 A
---------------	-----

**Cable**

Cable diameter	7 mm
----------------	------

**Connection**

Conductor cross-section	0.75 - 0.75 mm <sup>2</sup>
-------------------------	-----------------------------

**Equipment**

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

**Materials**

Colour	White
--------	-------

**Cable**

Cable permanent temperature resistant to	90 °C
--	-------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes