



K7B1M1W

### 10A Luminaire Lead 1.5m 1mm 3 Core Plug to Wire

#### Technical Features

##### Architecture

Number of poles	2
-----------------	---

##### Voltage

Max. operating voltage	240 V
------------------------	-------

##### Electric current

Rated current	10 A
---------------	------

##### Cable

Cable diameter	8 mm
----------------	------

##### Connection

Conductor cross-section	1 - 1 mm <sup>2</sup>
-------------------------	-----------------------

##### Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

##### Materials

Colour	White
--------	-------

##### Cable

Cable permanent temperature resistant to	90 °C
--	-------

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes