



K7J9M1W

### 10A Luminaire Lead 9m 1mm 4 Core Plug to Wire

#### Technical Features

##### Architecture

Number of poles	3
-----------------	---

##### Voltage

Max. operating voltage	240 V
------------------------	-------

##### Electric current

Rated current	6 A
---------------	-----

##### Cable

Cable diameter	8 mm
----------------	------

##### Connection

Conductor cross-section	0.75 - 0.75 mm <sup>2</sup>
-------------------------	-----------------------------

##### Equipment

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

Type of cable	Device connection cable
---------------	-------------------------

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

##### Materials

Colour	White
--------	-------

##### Cable

Cable permanent temperature resistant to	90 °C
--	-------

##### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----