



**SCHUKO socket outlet, K.5, Aluminium, aluminium anodised**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	Aluminium
Material	Aluminium
Treatment	Anodised

**Dimensions**

Height	71 mm
Width	71 mm
Depth	43 mm
Built-in depth flush-mounted boxes	31 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Mounting type	Claw mounting Screw connection
---------------	-----------------------------------

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

With enhanced contact protection	Yes
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	Without imprint
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

**Suitable for**

K.x	
-----	--

**Sustainability**

Halogen free	Yes
RoHS conform	Yes