




TYAS664AN



Dimmer 4 channels 300w with parallelization KNX Secure

Technical Features

Voltage

Operating voltage over bus	21 - 32 V
Input voltage	230 - 230 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connectivity

With bus system KNX radio	No
Type of connection	quickconnect

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Texts

Fuse	Overheating protection (display using LEDs) Short-circuit proof and overload-proof (display using LEDs)
Dimming principle	Phase cut-on or cut-off according to load type, self-learning Minimum/maximum dimming values per channel settable on device
Function	Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus
Type of connection	With quickconnect plug-in terminals
Labelling	Large labelling field
Protection	With overheating, overload and short-circuit protection

Sustainability

RoHS conform	Yes
--------------	-----