



WMSSU83FON!HTG

13A FCU Switched with LED Indicator and Flex Outlet Marked HEATING

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth	25.30 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Electric current

Rated current	13 A
---------------	------

Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	With control LED for ON
Switch mode	2-pole

Sustainability

RoHS conform	Yes
--------------	-----