



WMDP84!FRE

**20A Double Pole Switch Marked FREEZER**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 21.90 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Single rocker

**Electric current**

Rated current 20 A

**Texts**

Lighting With control LED for ON

Switch mode 2-pole

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes