



TXA111



**Power supply 30V DC 320 mA**

**Technical Features**

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

**Electric current**

|                |        |
|----------------|--------|
| Output current | 320 mA |
|----------------|--------|

**Connectivity**

|                           |    |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

**Voltage**

|                |           |
|----------------|-----------|
| Output voltage | 28 - 32 V |
|----------------|-----------|

**Connection**

|                                  |                            |
|----------------------------------|----------------------------|
| Cross-section flexible conductor | 0.75 - 2.5 mm <sup>2</sup> |
| Cross-section rigid conductor    | 0.75 - 2.5 mm <sup>2</sup> |

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Connectivity**

|                    |              |
|--------------------|--------------|
| Type of connection | quickconnect |
|--------------------|--------------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Power supply**

|                |          |
|----------------|----------|
| Supply voltage | 230 V AC |
|----------------|----------|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |