



TXA111



Napojna jedinica, 320mA, KNX, REG

Tehničke karakteristike

Kapacitet

Broj modula	4
-------------	---

Električna struja

Izlazna struja	320 mA
----------------	--------

Povezivost

Sa bus sistemom KNX radio	Ne
---------------------------	----

Napon

Izlazni napon	28 - 32 V
---------------	-----------

Veza

Presjek fleksibilnog vodiča	0.75 - 2.5 mm ²
-----------------------------	----------------------------

Presjek krutog provodnika	0.75 - 2.5 mm ²
---------------------------	----------------------------

Uvjeti korištenja

Radna temperatura	-5 - 45 °C
-------------------	------------

Povezivost

Vrsta veze	quickconnect
------------	--------------

Frekvencija

Frekvencija	50 - 60 Hz
-------------	------------

Napajanje

Napon napajanja	230 V AC
-----------------	----------

Održivost

REACH-bez SVHC	Da
----------------	----

Usklađeno sa RoHS	Da
-------------------	----