



JPA3600M20TX1

**Single chassis, apex, 36 Pole, 200A MCCB Twin, 6 Modules, orange, 1000x600x200mm**

**Technical Features**

**Connection**

Number of accessible phases 36

**Installation, mounting**

Mounting on Surface mounting

**Electric current**

Rated current 200 A

Breaking and opening capacity I<sub>dm</sub> 0 kA

**Equipment**

With lock Yes

Has mounting plate No

Equipped with switch No switch

Number of switches 0

Type of busbar chassis Fixed load chassis

**Capacity**

Number of modules 16

**Weight**

Weight 44 kg

**Dimensions**

Height 1000 mm

Width 600 mm

Depth 200 mm

**Cover, door**

Door/cover is transparent No

**Materials**

Material Steel

Colour Orange

**Safety**

Protection class Isolation class I

Impact resistance IK IK05

Ingress Protection (IP) class IP43

Locking type 3-point lever  
Key lock

**Architecture**

Number of poles 36