
Product Datasheet
JPA4800NSSTX



JPA4800NSSTX1

Single chassis, apex, 48 Pole,250A Direct Twin, 6 Modules, orange,1200x600x200mm

Technical Features

Connection

Number of accessible phases	48

Installation, mounting

Mounting on	Surface mounting

Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Fixed load chassis

Capacity

Number of modules	16

Weight

Weight	48 kg

Dimensions

Height	1200 mm
Width	600 mm
Depth	200 mm

Cover, door

Door/cover is transparent	No

Materials

Material	Steel
Colour	Orange

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP43
Locking type	3-point lever Key lock

Architecture

Number of poles	48

Sustainability

RoHS conform	Yes