Product Datasheet
JPA4800S25TW



JPA4800S25TW1

Single chassis, apex, 48 Pole,250A Isolator Twin, 6 Modules, grey,1200x600x200mm

Technical Features

Connection

Number of accessible phases	48

Installation, mounting

Mounting on	Surface mounting

Electric current

Rated current IN	250 A

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	Isolator
Number of switches	1
Type of busbar chassis	Fixed load chassis

Capacity

Number of modules	16

Weight

Weight	50 kg

Dimensions

Height	1200 mm
Width	600 mm
Depth	200 mm

Cover, door

Door/cover is transparent	No

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP43
Locking type	3-point lever Key lock

Architecture

Number of poles	48

Sustainability

RoHS conform	Yes