Product Datasheet
JPA9600NSSTW



JPA9600NSSTW1

Single chassis, apex, 96Pole, 250A Direct Twin, 6 Modules, grey, 1600x600x200mm

Technical Features

Connection

Number of accessible phases	96

Installation, mounting

Mounting on	Surface mounting

Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Fixed load chassis

Capacity

Number of modules	16

Weight

Weight	61 kg

Dimensions

Height	1600 mm
Width	600 mm
Depth	200 mm

Cover, door

Door/cover is transparent	No

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP43
Locking type	3-point lever Key lock

Architecture

Number of poles	96

Sustainability

RoHS conform	Yes