




EE883



Circulation sensor HF

Technical Features

Detection

Detection angle	360 - 360
Type of sensor	Movement detector

Settings

Time delay	5 S - 15 Min
------------	--------------

Lighting

Response brightness adjustable	2 - 1000 lx
--------------------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Dimensions

Recommended installation height	2.50 - 2.50 m
---------------------------------	---------------

Use conditions

Operating temperature	-20 - 50 °C
-----------------------	-------------

Materials

Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC)
----------	---

Safety

Ingress Protection (IP) class	IP54
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Texts

Function	Parallel connection of several detectors in order to expand the detection area
Installation mode	For ceiling mounting

Sustainability

RoHS conform	Yes
--------------	-----