



WBM10I-MW

**Mechanism 10A intermediate MW**

**Technical Features**

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Materials**

|                |           |
|----------------|-----------|
| Colour         | White     |
| Surface finish | Matt      |
| Treatment      | Varnished |

**Identification**

|                      |                                        |
|----------------------|----------------------------------------|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|----------------------------------------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

**Dimensions**

|            |            |
|------------|------------|
| Dimensions | 27 x 27 mm |
|------------|------------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

**Connection**

|                     |          |
|---------------------|----------|
| Connector/plug type | RotoLoc® |
|---------------------|----------|

**Texts**

|                    |                                          |
|--------------------|------------------------------------------|
| Installation mode  | RotoLoc®                                 |
| Type of connection | With screw terminals                     |
| Lighting           | Without lighting (cannot be illuminated) |
| Switch mode        | Intermediate                             |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |