



WBSP1S-MW

**Silhouette 10A socket Horz + shutter MW**

**Technical Features**

**Electric current**

Rated current	10 A
---------------	------

**Voltage**

Nominal voltage	250 - 250 V
-----------------	-------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
--------	-------

Surface finish	Matt
----------------	------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Varnished
-----------	-----------

**Dimensions**

Height	77 mm
--------	-------

Width	117 mm
-------	--------

Depth	28 mm
-------	-------

Built-in depth	23 mm
----------------	-------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
-----------------------------------	---------------------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Functions**

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

**Texts**

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
-------	------------------

Protection	Enhanced contact protection
------------	-----------------------------

Type of connection	With screw terminals
--------------------	----------------------

**Suitable for**

silhouette	
------------	--

**Sustainability**

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----