




WBME5A



Mechanism, 5A electronic push button

Technical Features

Connectivity

With bus system KNX radio No

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Material Polycarbonate (PC)

Dimensions

Built-in depth 45 mm

Depth 45 mm

Architecture

Control/operation element Push button

Power

Power consumption standby 0.35 W

230 V incandescent and halogen lamp 1200 W

Lighting

LED lamp power 500 W

Use conditions

Operating temperature 5 - 40 °C

Connection

Cross-section rigid conductor 1 - 2.5 mm²

Capacity

Number of modules 1

Texts

Installation mode RotoLoc®

Type of connection With screw terminals

Extension unit input With extension unit input for slave push-button WBMESL

Equipment

Substation input No

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes