



WBSSV5

Silhouette 5G Switch Vert

Technical Features

Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

|                |                    |
|----------------|--------------------|
| Colour         | White              |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |

Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 5 |
|-------------------|---|

Dimensions

|                |             |
|----------------|-------------|
| Dimensions     | 117 x 77 mm |
| Built-in depth | 23 mm       |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Texts

|                    |                           |
|--------------------|---------------------------|
| Installation mode  | For screw fastening       |
| Type of connection | With screw terminals      |
| Switch mode        | 2-way, with loop terminal |

Sustainability

|              |     |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |