



WXPSS81

IP66 Weatherproof 1G 13A DP Switched Socket

Technical Features

Electric current

Rated current	13 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Materials

Colour	Light grey
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Depth	88.25 mm
-------	----------

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Hinged cover falls back, manual clip-in
-------------	---

Capacity

Number of modules	0
-------------------	---

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes