



WBSP1S

### Silhouette 10A socket Horz + shutter

#### Technical Features

##### Electric current

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

##### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 250 - 250 V |
|-----------------|-------------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

##### Materials

|                |                    |
|----------------|--------------------|
| Colour         | White              |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |

##### Dimensions

|                |        |
|----------------|--------|
| Height         | 77 mm  |
| Width          | 117 mm |
| Depth          | 28 mm  |
| Built-in depth | 23 mm  |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type      | Screw mounting |

##### Equipment

|                                   |                                 |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert            | No                              |
| With hinged lid                   | No                              |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

##### Texts

|                    |                             |
|--------------------|-----------------------------|
| Imprint            | Without imprint             |
| Cover              | Full cover plate            |
| Protection         | Enhanced contact protection |
| Type of connection | With screw terminals        |

##### Suitable for

|            |  |
|------------|--|
| silhouette |  |
|------------|--|

##### Sustainability

|              |     |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |