



WBSSV6

### Silhouette 6G Switch Vert

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	6
-------------------	---

##### Dimensions

Dimensions	117 x 77 mm
Built-in depth	23 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Electric current

Rated current	16 A
---------------	------

##### Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Switch mode	2-way, with loop terminal

##### Sustainability

Halogen free	Yes
RoHS conform	Yes