



HMQ971AR

Load Break Switch Disconnecter h3+ PW1600 4P 1000A FTC

Technical Features

Electric current

Rated current	1000 A
Rated short-time withstand current I _{cw} IEC 60947	19.2 kA
Rated current 10°C according to IEC 60947	1000 A
Rated current 15°C according to IEC 60947	1000 A
Rated current 20°C according to IEC 60947	1000 A
Rated current 25°C according to IEC 60947	1000 A
Rated current 30°C according to IEC 60947	1000 A
Rated current at 35°C according to IEC 60947	1000 A
Rated current at 40°C according to IEC 60947	1000 A
Rated current 45°C according to IEC 60947	1000 A
Rated current 50°C according to IEC 60947	1000 A
Rated current 55°C according to IEC 60947	1000 A
Rated current at 60°C according to IEC 60947	1000 A
Rated current 65°C according to IEC 60947	1000 A
Rated current 70°C according to IEC 60947	1000 A

Architecture

Number of poles	4
Control/operation element	Toggle

Voltage

Rated insulation voltage U _i	1000 V
Rated impulse withstand voltage U _{imp}	8 kV

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Trip unit	Switch
-----------	--------

Sustainability

RoHS conform	Yes
--------------	-----