



WGDS113SNB

**13A SINGLE SWITCHED SOCKET, NB**

**Technical Features**

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Electric current**

|                |      |
|----------------|------|
| Output current | 0 mA |
| Rated current  | 13 A |

**Voltage**

|                |       |
|----------------|-------|
| Output voltage | 0-0 V |
|----------------|-------|

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Power**

|                           |     |
|---------------------------|-----|
| Output power              | 0 W |
| Power consumption standby | 0 W |

**Materials**

|  |                    |
|--|--------------------|
| Colour   | White              |
| Surface finish   | Glossy             |
| Material   | Polycarbonate (PC) |
| Treatment  | Untreated          |
| Contains recycled material (% of total plastic weight) | 0 %                |

**Dimensions**

|        |       |
|--------|-------|
| Height | 30 mm |
| Width  | 86 mm |
| Depth  | 18 mm |

**Cable**

|              |     |
|--------------|-----|
| Cable length | 0 m |
|--------------|-----|

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth                     | 18 mm |

**Connection**

|  |                          |
|--|--------------------------|
| Connector/plug type                                      | British Standard         |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm <sup>2</sup> |
| Number of conduit inlets                                 | 0                        |

**Installation, mounting**

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Back           |

**Connectivity**

|                         |                  |
|-------------------------|------------------|
| Type of connection      | Screw terminal   |
| With claw mounting      | No               |
| Mounting type           | Screw mounting   |
| Connector/plug type USB | British Standard |

**Equipment**

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | Yes              |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |
| With signal lamp                  | No               |

---

**Equipment**

---

|           |    |
|-----------|----|
| With lock | No |
|-----------|----|

---

**Accessories**

---

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

---

|                   |      |
|-------------------|------|
| Pre-equipped with | None |
|-------------------|------|

---

**Capacity**

---

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

---

**Safety**

---

|                                  |    |
|----------------------------------|----|
| With enhanced contact protection | No |
|----------------------------------|----|

---

|                      |      |
|----------------------|------|
| Impact resistance IK | IK02 |
|----------------------|------|

---

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

---

**Functions**

---

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
|---------------------------|----|

---

|                        |    |
|------------------------|----|
| With function lighting | No |
|------------------------|----|

---

**Identification**

---

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

---

**Suitable for**

---

|       |  |
|-------|--|
| shark |  |
|-------|--|

---

**Sustainability**

---

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

---

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

---

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

---