



TYBS794A



Binary input 4 fold + LED output 4 fold, flush mounted, KNX

Technical Features

Architecture

Bus system	EIB
------------	-----

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Electric current

Number of entry circuits	8
--------------------------	---

Equipment

External signal voltage necessary	No
-----------------------------------	----

Connectivity

With bus system KNX radio	No
---------------------------	----

Equipment

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Lighting

LED controlling	No
-----------------	----

Materials

Material	Plastic
Colour	Light grey
RAL code	7035

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5-+45 °C
-----------------------	-----------

Cable

Cable length	0.25 m
--------------	--------

Voltage

Input voltage	5-5 V
Operating voltage over bus	21-32 V
Type voltage supply	DC
System supply voltage	30 V DC Via bus

Dimensions

Length	43.5 mm
Height	35.5 mm
Depth	15.4 mm

Texts

Installation mode	For flush-mounted and hollow wall mounting
Type of connection	With pre-assembled cable

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes