



TYBS702A

**Binary input 2 fold, flush mounted, KNX**

**Technical Features**

**Architecture**

Bus system	KNX
------------	-----

**Settings**

Supported configuration mode	ETS easy
------------------------------	----------

**Electric current**

Number of entry circuits	2
--------------------------	---

**Equipment**

External signal voltage necessary	No
-----------------------------------	----

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Equipment**

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Lighting**

LED controlling	No
-----------------	----

**Materials**

Material	Plastic
Colour	Light grey
RAL code	7035

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - +45 °C
-----------------------	-------------

**Cable**

Cable length	0.25 m
--------------	--------

**Voltage**

Input voltage	3.3-3.3 V
Operating voltage over bus	21-32 V
Type voltage supply	DC
System supply voltage	30 V DC Via bus

**Dimensions**

Length	43 mm
Height	28.5 mm
Depth	15.4 mm

**Texts**

Installation mode	For flush-mounted and hollow wall mounting
Type of connection	With pre-assembled cable

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes