



WNA104B

cubyko Socket 2P+E with label holder composable white IP55

Technical Features

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Pure white
RAL code	9010
Material	Polycarbonate (PC) Polypropylene (PP)

Dimensions

Height	75 mm
Width	75 mm
Depth	22.80 mm
Built-in depth flush-mounted boxes	40 mm

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Installation, mounting

Mounting on	Flush mounting Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
Mounting type	Click mounting

Equipment

Connector/plug type socket outlet	French norm NF
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK08
Ingress Protection (IP) class	IP55

Functions

With orientation lighting	No
---------------------------	----

Identification

With imprint	No
--------------	----

Texts

Cover	For covering of socket outlets
Protection	Without protective screen

Suitable for

cubyko

Sustainability

Halogen free

Yes

RoHS conform

Yes