



TJAS671

**domovea basic**

**Technical Features**

**Equipment**

Web server	Yes
------------	-----

**Voltage**

Operating voltage	195 - 254 V
Operating voltage over bus	21 - 32 V
Type voltage supply	AC

**Connectivity**

Type of interface bus system/media gateway	Multiple interface
--	--------------------

**Settings**

Supported configuration mode	ETS easy
------------------------------	-------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Equipment**

Number of channels	1
--------------------	---

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Controls and indicators**

With LED indication	Yes
---------------------	-----

**Dimensions**

Width	106 mm
Dimensions	90 x 106 mm
Depth	65 mm
Number of width units	6

**Connection**

Connector/plug type Bus system	Bus connection terminal
Connector/plug type	quickconnect

**Texts**

Encoding	Management of 4 configurable user profiles
Connectors jacks	With 2 USB sockets type A
Type of connection	With quickconnect plug-in terminals