



TJAS471

domovea plus

Technical Features

Equipment

Web server	Yes
------------	-----

Voltage

Operating voltage	195 - 254 V
Operating voltage over bus	21 - 32 V
Type voltage supply	AC

Connectivity

Type of interface bus system/media gateway	Multiple interface
--	--------------------

Settings

Supported configuration mode	easy ETS
------------------------------	-------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Equipment

Number of channels	1
--------------------	---

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Controls and indicators

With LED indication	Yes
---------------------	-----

Dimensions

Width	106 mm
Dimensions	90 x 106 mm
Depth	65 mm
Number of width units	6

Connection

Connector/plug type Bus system	Bus connection terminal
Connector/plug type	quickconnect

Texts

Encoding	Management of 4 configurable user profiles
Connectors jacks	With 2 USB sockets type A
Type of connection	With quickconnect plug-in terminals