



TYBS601B



**Output module 1x 10A /230V~, flush mounted, KNX**

### Technical Features

#### Settings

Supported configuration mode	ETS easy
------------------------------	-------------

#### Connectivity

With bus system KNX	Yes
With bus system KNX radio	No

#### Dimensions

Dimensions	44 x 43 mm
Height	44 mm
Width	43 mm
Depth	22 mm
Built-in depth	40 mm

#### Electric current

Rated current	10 A
---------------	------

#### Materials

Colour	Light grey
--------	------------

#### Equipment

Radio frequency bidirectional	No
With switch for manual switch	Yes

#### Electric current

Bus current consumption while idle	5 mA
------------------------------------	------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Power incandescent lamp 230 V	600 - 600 W
Output power	500 W
230 V incandescent and halogen lamp	600 W

#### Voltage

Rated operational voltage Ue	230 - 230 V
System supply voltage	30 V DC Via bus
Operating voltage over bus	21 - 32 V

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

#### Connection

Cross-section rigid conductor	0.75 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor	0.75 - 2.5 mm <sup>2</sup>

#### Texts

Type of connection	With screw terminals
--------------------	----------------------

#### Sustainability

RoHS conform	Yes
--------------	-----