



IU39S

**3 Row, 39M din rail board, Surface**

**Technical Features**

**Voltage**

|                 |             |
|-----------------|-------------|
| Nominal voltage | 230 - 230 V |
|-----------------|-------------|

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Equipment**

|                            |     |
|----------------------------|-----|
| Number of rails            | 3   |
| Number of rows             | 3   |
| Has neutral terminal block | Yes |

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 39 |
|-------------------|----|

**Dimensions**

|        |        |
|--------|--------|
| Height | 530 mm |
| Width  | 355 mm |
| Depth  | 115 mm |

**Cover, door**

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

**Dimensions**

|                |        |
|----------------|--------|
| Built-in depth | 110 mm |
|----------------|--------|

**Cover, door**

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

**Dimensions**

|                       |    |
|-----------------------|----|
| Number of width units | 13 |
|-----------------------|----|

**Cover, door**

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

**Connection**

|                          |   |
|--------------------------|---|
| Number of conduit inlets | 4 |
|--------------------------|---|

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Materials**

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9002       |
| Colour   | Grey white |

**Equipment**

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

**Safety**

|                               |                   |
|-------------------------------|-------------------|
| Protection class              | Isolation class I |
| Impact resistance IK          | IK05              |
| Ingress Protection (IP) class | IP40              |
| Locking type                  | Without lock      |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|